


YL-100 Automatic Cartoning Machine



Instruction:

Automatic Cartoning Machine can suitable for pharmaceuticals product into carton, such as liquid in bottle(glass/flat), vial, tube/ointment, capsule/tablet blister, plaster, soft strips, injection, tray, syringe, ampoule and condom and sachet/pouch and other products. The machine finished running by a series of photo-electro controller to make the machine stability and guarantee the packing quality. It includes 1to 4folds leaflet automatic folding, cantons in suction and forming, products and leaflet insert into carton, printing batch number, sealing by tuck-in or hot-glue device. The machine can be single used or linked with label machine, tube sealing and filling Machine, blister packing machine, shrink machine, overwrapping machine, bundling machine and case packer to form a production line.



Main Technical Parameters

Encasing Speed		30-100 Boxes/min
Box	Quality Requirement	250-350g/m ²
	Dimension Range (L×W×H)	(70-180)×(35-85)×(15-50)mm
	Quality Requirement	60-70g/m ²
Leaflet	Unfolded Leaflet Specification (L×W)	(80-250)×(90-170)mm
	Fold Range	(1-4) Fold
	Working Pressure	≥ 0.6mpa
Compressed Air	Air Consumption	120-160L/min
	Power	220V/50Hz
Motor Power		0.75Kw
Machine Dimension(L×W×H)		3100×1100×1550mm
Machine Weight		1500Kg

Notes:If any change of data,we will not notify further.

YL-100P Automatic Cartoning Machine For Bottle

Instruction:

Automatic Cartoning Machine can suitable for bottle (glass/flat), vial into one carton. The machine finished running by a series of photo-electro controller to make the machine stability and guarantee the packing quality. It includes 1to 4folds leaflet automatic folding, cantons in suction and forming, products and leaflet insert into carton, printing batch number, sealing by tuck-in or hot-glue device. The machine can be single used or linked with label machine, shrink machine, overwrapping machine, bundling machine and case packer to form a production line.

Feature:

- 1.International famous brand of electrical component such as PLC touch screen, frequency inverters, etc.
- 2.Adopt human-machine operation system.
- 3.Automatically displaying device for trouble, speed and finished products counting.
- 4.Machine running without pressing if no products or incorrect position of products. And stopping automatically if incorrect position of product into carton after return or no cartons or out of leaflets continuous.
- 5.No products not suction leaflet, no leaflet not suction carton.
- 6.Automatic detection and rejection device for lacking blister goods and leaflets.



Main Technical Parameters

Encasing Speed		30-100 Boxes/min
Box	Quality Requirement	250-350g/m ²
	Dimension Range (L×W×H)	(70-180)×(35-85)×(15-50)mm
	Quality Requirement	60-70g/m ²
Leaflet	Unfolded Leaflet Specification (L×W)	(80-250)×(90-170)mm
	Fold Range	(1-4) Fold
	Working Pressure	≥ 0.6mpa
Compressed Air	Air Consumption	120-160L/min
	Power	220V/50Hz
Motor Power		0.75Kw
Machine Dimension(L×W×H)		4300×1100×1550mm
Machine Weight		1600Kg

Notes:If any change of data,we will not notify further.